

# Identification File of Type ZE64G23 for use in oil

# CONTENTS

	Page No.
1. Category	1
2. Structure	1
3. Manufacturing process	2
4. Manufacturing control	2
5. Shop and acceptance test	3
6. Electrical characteristics	5
7. Other information	6
Fig.1 Power consumption - temperature characteristic	7
Fig.2 Resistive current - temperature characteristics	7
Fig.3 Total leakage current - temperature characteristic	8
Fig.4 Accelerated ageing test result	8
Fig.5 Residual voltage ratio - discharge current characteristics	9
Fig.6 Protective characteristics	9
Fig.7 Absorbed energy - discharge current characteristic	10
Fig.8 Discharge current - operation times characteristic	10

April , 2005

MEIDENSHA CORPORATION



#### Identification File

#### 1. Category

Zinc oxide block described in this file is applied to the arrester for use in oil.

#### 2. Structure

#### (a) General


The side surface of block is covered with high resistance layers. The both contact surfaces are spray coated with aluminum.

### (b) Dimension and reference number

Reference	Dimensio	n ( mm )	Volume	Weight	
Number	Diameter	Thickness	( cm <sup>3</sup> )	(g)	
ZE64G23	64.5 ± 1.0	22.5 ± 1.0	73.6 ± 5.6	407 ± 36	

#### (c) Indication

Following figures are indicated on each block.



#### (Note)


- 1. The month of October, November and December are indicated as X, Y, and Z respectively.
- 2. Range of V1mA ( dc ) is shown as follows.

Range of V1mA (dc)

Туре	V1mA ( dc ) ( kV )	Range
	4.28 ~ 4.32	L4
ZE64G23	4.33 ~ 4.37	L3
	4.38 ~ 4.42	L2




# ( d ) Construction The block consists of following parts



#### 3. Manufacturing process

Zinc oxide, additives of Bi2O3 , Co3O4 , MnO2 , Cr2O3 , Sb2O3 , etc. and pure water are mixed and granulated. After granulation, press forming and sintering were performed. The manufacturing flow is as follows.



#### 4. Manufacturing control

The quality system meets the requirements laid down in the International Standard ISO 9001.



#### 5. Shop and acceptance test

#### 5.1 Test procedure

(a) Dimension and appearance test

This test shall be carried out in the in-process inspection.

#### (b) Reference voltage test

Reference voltage defined as terminal voltage across ZnO block when d.c. 1mA begins to flow.

This test shall be carried out promptly in order to avoid heat generation of blocks and this test shall be made at a block temperature of 20 to 25 .

#### (c) Residual voltage test

Residual voltage at current impulse with 8/20us, 10kA shall be measured.

#### (d) Discharge current withstand capability

#### (I) High current impulse

The current impulse with 4/10us, 100kA shall be applied to the block for 2 times. The interval between impulses shall be long enough for the block to be cooled down to the ambient temperature.

#### ( ii ) Rectangular current impulse

The 2ms rectangular current impulse with 1,000A shall be applied to the block for 20 times. These divided into 4 groups of 5 impulses. The interval between impulses shall be 50 to 60 seconds and the interval between groups shall be long enough for the block to be cooled down to the ambient temperature.

#### 5.2 Sampling procedure

Sampling procedure shall be carried out in accordance with MIL - STD - 105E.

Test item	Number of samples	Remarks		
Reference voltage and external appearance	all blocks	In process inspection		
Residual voltage ratio at a specified current value	5 blocks / lot	MIL-STD-105E , S-2 Double sampling plan AQL = 6.5 %		
High current impulse withstand	5 blocks / lot	MIL-STD-105E , S-2 Double sampling plan AQL = 6.5 %		
Rectangular current impulse withstand	5 blocks / lot	MIL-STD-105E,S-2 Double sampling plan AQL = 6.5 %		
Dimension check	50 blocks / lot	MIL-STD-105E,S-4 Single sampling plan AQL = 1.0 %		



The double sampling plan shall be as follows.

First sampling test

Good	No good	Evaluation	
5	0	Acceptable	
4	1	Re-sampling	
0 - 3	2 - 5	Not acceptable	

Re-sampling test (total)

to camping toot ( total )					
Good	No good	Evaluation			
9	1	Acceptable			
4 - 8	2 - 6	Not acceptable			

The single sampling plan shall be as follows.

Sampling test

Good	No good	Evaluation
49 - 50	0 - 1	Acceptable
0 - 48	2 - 50	Not acceptable

(Note)

- 1. Reference voltage test and external appearance check shall be carried out on each ZnO block in the in process inspection.
- 2. The number of samples shall be based on 5,000 blocks.



# 6. Electrical characteristics

(a)	Rated discharge current				10	kAcrest
(b)	MCOV in oil up to 110				1.6	kVrms
(c)	Reference voltage V1mA ( ac ) [ V1mA ( dc )	( at	25	)		~ 4.42 kVcrest ~ 4.42 kVcrest ]
(d)	Power consumption at MCOV Average Max.	( at	90	)	0.27 0.41	W W
	Power consumption ( average ) -	Temper	ature	characteris	stic	Refer to Fig.1
(e)	Resistive current at MCOV Average Max.	( at	90	)	0.27 0.41	mAcrest mAcrest
	Resistive current ( average ) - Te	mperatu	ıre ch	aracteristic		Refer to Fig.2
(f)	Total leakage current at MCOV Average Max.	( at	90	)	0.67 1.00	mArms mArms
	Total leakage current ( average )	- Temp	eratur	e characte	ristic	Refer to Fig.3
(g)	Life cycle					
	Accelerated ageing test result					Refer to Fig.4
(h)	Residual voltage ratio at 10 kA Average Max.				1.65 1.69	( - ) ( - )
	Residual voltage ratio - discharge	current	chara	acteristics		Refer to Fig.5
	Protective characteristics ( Average	e value	)			Refer to Fig.6
(i)	High current withstand capability 10		00 kAcr	est - 2 shots		
(j)	Rectangular current withstand capa	ability		1	1,000 A	- 20 shots
	Absorved energy - discharge curr	ent cha	racteri	stic		Refer to Fig.7
	Discharge current – applicable nui	mber ch	aracte	eristic		Refer to Fig.8



#### 7. Other information

# 7.1 Minimum contact pressure of blocks

The minimum contact pressure of blocks shall be 10 kg.

# 7.2 Working capability

The working capability of blocks are defined by the weight of granulation powder at Meidensha.

The working capability of Meidensha is about 600 tons per year ( as of August 1993 ).



